



SPN715D

**SPD 2P auto-protected pluggable 15kA class 2 with end of life indicator**

**Technical properties**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage $U_e$	230 V
Frequency	50/60 Hz
Nominal discharge current ( $I_n$ ) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	5 kA

**Voltage**

Maximum continuous operating voltage $U_c$	275 V
Voltage protection level $U_p$ according to IEC61643-1	1.5 kV

**Electric current**

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	15 kA
--	-------

**Dimensions**

Depth of installed product	70 mm
Width of installed product	36 mm

**Power**

Total power loss under $I_N$	0 W
------------------------------	-----

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
---	-------------------

**Standards**

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

**Use conditions**

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C