



SPN800

## SPD 3P pluggable 75kA class 1 with end of life indicator TNC

### Technical properties

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

#### Main electrical features

|                              |          |
|------------------------------|----------|
| Test class type1 IEC61643-11 | Yes      |
| Frequency                    | 50/60 Hz |

#### Electric current

|                                     |       |
|-------------------------------------|-------|
| Max discharge (Imax) L-N(PEN)/ N-PE | 75 kA |
|-------------------------------------|-------|

#### Dimensions

|                            |        |
|----------------------------|--------|
| Depth of installed product | 83 mm  |
| Width of installed product | 108 mm |

#### Power

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 0 W |
|---------------------------|-----|

#### Network configuration

|              |      |
|--------------|------|
| Network type | TN-C |
|--------------|------|

#### Standards

|                                       |           |
|---------------------------------------|-----------|
| Test class IEC61643-11 / VDE0675-6-11 | T1        |
| European directive WEEE               | concerned |

#### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -40...60 °C |
| Storage/transport temperature | -40...80 °C |