



SPK602

Surge protection for ADSL DIN-Rail

Technical properties

Configuration

Earthing via	Separate conductor
--------------	--------------------

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Rated operational voltage Ue	130 V
Nominal voltage	130 V

Voltage

Maximum continuous operating voltage Uc	185 V
Rated operational voltage in DC	185 V
Voltage protection level Up according to IEC61643-1	300 V
Maximum continuous operating voltage Uc DC IEC61643	185 V

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	10 kA
-------------------------------------	-------

Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	17.7 mm
Width	17.7 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Installation, mounting

Tightening torque	0.5Nm
Mounting type	din-Rail

Connection

Type of connection	with screw
--------------------	------------

Standards

Approvals	CE, KEMA
Test class IEC61643-11 / VDE0675-6-11	B2 ; C1 ; C2 ; C3 ; D1

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-40...85 °C
Storage/transport temperature	-40...85 °C