



SPK806

Surge protection IT for industrial bus networks

Technical properties

Configuration

Earthing via Separate conductor

Controls and indicators

Indicator lamp Optic

Main electrical features

Rated operational voltage Ue 0 / 12 V DC

Nominal voltage 12 V DC

Voltage

Maximum continuous operating voltage Uc 15 V

Rated operational voltage in DC 24 V

Voltage protection level Up according to IEC61643-1 80 V

Maximum continuous operating voltage Uc DC IEC61643 30 V

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 10 kA

Dimensions

Depth of installed product 76 mm

Height of installed product 105.8 mm

Width of installed product 6.2 mm

Width 6.2 mm

Frequency

Frequency 50 to 60 Hz

Installation, mounting

Mounting type din-Rail

Connection

Type of connection with screw

Standards

Approvals CE, KEMA

Test class IEC61643-11 / VDE0675-6-11 C1 ; C2 ; C3 ; D1

Safety

REACH conform No

RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-40...85 °C
Storage/transport temperature	-40...85 °C