



ST313



## Safety transformer 16VA 230V12-24V

### Technical properties

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4000 V
Output voltage 2	24 V
Open circuit voltage secondary	15.8 / 30 V
Output voltage	12 / 24 V

#### Electric current

Output intensity 2	0.67 A
Output intensity	1.33 A

#### Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Power consumed	16 VA
Total power loss under IN	1.5 W

#### Power supply

Transformer	Safety transformer to
-------------	-----------------------

#### Installation, mounting

Tightening torque	1,2Nm
Suitable for surface mounting	Yes
Suitable for flush-mounting	No
Mounting type	din-Rail

#### Connection

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

#### Cable

Max. cable length to door actuator release 0.5 A	max. 100 m
Max. cable length to door actuator release 1 A	max. 50 m
<b>Equipment</b>	
On/Off switch	No
Short-circuit protected	Yes
<b>Standards</b>	
Standard text	EN 61558-2-6
Approvals	EN 61558-2-6
<b>Safety</b>	
Temperature protection	Yes
<b>Use conditions</b>	
Operating temperature	-20...35 °C
Altitude	<= 2000 m