



SPK900

## Surge protection RJ45 for Ethernet and VoIP networks

### Technical properties

#### Configuration

Earthing via Separate conductor

#### Controls and indicators

Indicator lamp no

#### Voltage

Maximum continuous operating voltage  $U_c$  3.3 V

Voltage protection level  $U_p$  according to IEC61643-1 100 V

Maximum continuous operating voltage  $U_c$  DC IEC61643 3.3 V

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 10 kA

#### Dimensions

Depth of installed product 57.5 mm

Height of installed product 100 mm

Width of installed product 25 mm

Width 25 mm

#### Frequency

Frequency 50 to 60 Hz

#### Installation, mounting

Mounting type din-Rail

#### Connection

Type of connection RJ45 connectors or Quickconnect

#### Standards

Approvals CE, KEMA

Test class IEC61643-11 / VDE0675-6-11 B2 ; C1 ; C2 ; C3 ; D1

European directive WEEE concerned

#### Use conditions

Operating temperature -40...85 °C

Storage/transport temperature -40...70 °C