



SVN125

Clear LED Indicator light 230VAC

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|---------------------------------|----------|
| Rated operational voltage U_e | 230 V |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 250 V |
| Rated impulse withstand voltage | 4000 V |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 62 mm |
| Height of installed product | 83 mm |
| Width of installed product | 17.5 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.8 W |
|---------------------------|-------|

Lighting control

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 1,7Nm |
|-------------------|-------|

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 6mm ² |
| Connection cross-sect. rigid cable | 0,75 / 10mm ² |
| Lamp socket type | Fix |
| Type of connection | with screw |

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|--|-------------|
| Operating temperature | -20...50 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |

Altitude

2000 m

Storage/transport temperature

-40...80 °C