




SVN332



## Latching 2NO Pushbutton

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Switching voltage	230 V

#### Electric current

Rated current	16 A
Momentary-contact current	16 A
Prospective short circuit withstand with MCB 16A B curve	1000A [Prot:16AcurveB]
Prospective short circuit withstand with fuse 16A gG	1000A [Prot:16AgG]
Thermal rated current outside of housings	16 A

#### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

#### Materials

Colour	not applicable
--------	----------------

#### Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

#### Standards

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-20...50 °C
-----------------------	-------------

---

Degree of pollution according to IEC 60664 / IEC 60947-2	3
---	---

---

Altitude	2000 m
----------	--------

---

Storage/transport temperature	-40...80 °C
-------------------------------	-------------