



SPN265R

## SPD 2P pluggable 65kA class 2 with reserve + remote contact

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50/60 Hz
Nominal discharge current ( $I_n$ ) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	20 kA

#### Voltage

Maximum continuous operating voltage $U_c$	275 V
Voltage protection level $U_p$ according to IEC61643-1	1.5 kV

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	65 kA
--	-------

#### Dimensions

Width of installed product	36 mm
----------------------------	-------

#### Power

Total power loss under $I_N$	0 W
------------------------------	-----

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

#### Use conditions

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C