



SPN415D

SPD 4P pluggable 15kA class 2 with end of life indicator

Technical properties

Architecture

Type of pole	3P+N
--------------	------

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (In) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	5 kA
---	------

Voltage

Maximum continuous operating voltage Uc	275 V
---	-------

Voltage protection level Up according to IEC61643-1	1 kV
---	------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	15 kA
-------------------------------------	-------

Dimensions

Width of installed product	72 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------