



SVN411

~ ~ ~ ~ ~

~ ~ ~ ~ ~

## Impulse 1NO Pushbutton + green Indicator light 230VAC

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Switching voltage	230 V

#### Electric current

Rated current	16 A
Momentary-contact current	16 A
Prospective short circuit withstand with MCB 16A B curve	1000A [Prot:16AcurveB]
Prospective short circuit withstand with fuse 16A gG	1000A [Prot:16AgG]
Thermal rated current outside of housings	16 A

#### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0.8 W
---------------------------	-------

#### Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

#### Materials

Colour	green
--------	-------

#### Lighting control

Type of lamp	LED
Lamp voltage	230 V

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>
Lamp socket type	Sans
Type of connection	with screw

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	1
Quantity of INV contacts	0

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C