



SPV025

Cartridge +/- for SPV325

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	12.5 kA
---	---------

Voltage

Maximum continuous operating voltage Uc	1000 V
---	--------

Voltage protection level Up according to IEC61643-1	4 kV
---	------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	25 kA
-------------------------------------	-------

Dimensions

Width of installed product	18 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------