



TCC510S



## Presence detector 360° monobloc KNX, white

### Technical properties

#### Architecture

Bus system	KNX
------------	-----

#### Connectivity

Number of binary inputs	0
-------------------------	---

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Electric current

Bus current consumption (data transfer)	10 mA
---	-------

#### Dimensions

Dimensions (Ø x H)	78 x 70 mm
Installation opening Ø	60...63 mm
Recommended installation height	2.5...3.5 m
Installation wall thickness	10...28 mm

#### Measurement

Detection Method	presence
------------------	----------

#### Detection

Detection angle	360 °
Detection angle	360 °
Angle of vertical detection	55 °
Detection field Ø, on floor	≈ 7 m
Detection field Ø, at desk height	≈ 5 m
Frontal detecting distance	7 m
Side detecting distance	8 m

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Surface appearance	matt

#### Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

#### Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

---

**Connection**

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

---

**Settings**

Supported configuration modes system

Delay time, adjustable 1 mn...1 h

---

**Scope of delivery**

Bus connection included Yes

---

**Equipment**

Number of channels 1

Angle of horizontal detection 360 °

---

**Use conditions**

Operating temperature -10...45 °C

Storage/transport temperature -20...60 °C

---

**Identification**

Main design line KNX