



TCC530E

IP41

## Presence detector 360° monobloc KNX

### Technical properties

#### Architecture

Bus system	KNX
------------	-----

#### Functions

Max. temporisation	480 mn
--------------------	--------

#### Connectivity

Number of binary inputs	0
-------------------------	---

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Dimensions

Dimensions (Ø x H)	78 x 70 mm
--------------------	------------

Installation opening Ø	60...63 mm
------------------------	------------

Recommended installation height	2.5...3.5 m
---------------------------------	-------------

Installation wall thickness	10...28 mm
-----------------------------	------------

#### Measurement

Detection Method	presence
------------------	----------

#### Detection

Detection angle	360 °
-----------------	-------

Detection angle	360 °
-----------------	-------

Angle of vertical detection	55 °
-----------------------------	------

Detection field Ø, on floor	≈ 7 m
-----------------------------	-------

Detection field Ø, at desk height	≈ 5 m
-----------------------------------	-------

Frontal detecting distance	7 m
----------------------------	-----

Side detecting distance	8 m
-------------------------	-----

#### Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Material	PC-ABS
----------	--------

Type of surface treatment	untreated
---------------------------	-----------

#### Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

#### Installation, mounting

**Connection**

---

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

---

**Settings**

---

Min. temporisation	5 s
Delay time, adjustable	1 mn...1 h

---

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

---

**Equipment**

---

Substation input	No
Number of channels	2
Bidirectional radio frequency	No
Angle of horizontal detection	360 °

---

**Use conditions**

---

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C

---