



ST303



Bell transformer 8VA 230V 8-12V

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 230 V |
| Frequency | 50 Hz |

Voltage

| | |
|--------------------------|----------|
| Rated insulation voltage | 4000 V |
| Output voltage 2 | 12 V |
| Output voltage | 8 / 12 V |

Electric current

| | |
|--------------------|--------|
| Output intensity 2 | 0.67 A |
| Output intensity | 1 A |

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 65 mm |
| Height of installed product | 111 mm |
| Width of installed product | 35 mm |

Power

| | |
|---------------------------|-------|
| Power consumed | 8 VA |
| Total power loss under IN | 2.2 W |

Installation, mounting

| | |
|-------------------------------|-------|
| Tightening torque | 1,2Nm |
| Suitable for surface mounting | Yes |
| Suitable for flush-mounting | No |

Connection

| | |
|---|------------------|
| Connection cross-sect. flexible conductor | 4mm ² |
| Connection cross-sect. rigid cable | 6mm ² |

Equipment

| | |
|-------------------------|-----|
| On/Off switch | No |
| Short-circuit protected | Yes |

Standards

| | |
|---------------|--------------|
| Standard text | EN 61558-2-6 |
|---------------|--------------|

Use conditions

Operating temperature

-20...35 °C

Altitude

≤ 2000 m