




TG353

IP44



## Big support for KNX weather station

### Technical properties

#### Functions

Precipitation (Yes/No)	1 bit
------------------------	-------

#### Controls and indicators

Button / push-button	with programming button
----------------------	-------------------------

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Dimensions

Dimensions (LLxwxhh)	40x16x6,5
Length, wall bracket	400 mm

#### Measurement

Measuring range, wind speed	0...35 m/s
-----------------------------	------------

#### Materials

Material	aluminium
----------	-----------

#### Connection

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

#### Equipment

Slewing	with an adjustable joint
---------	--------------------------

#### Use

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

#### Safety

Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-30...50 °C
-----------------------	-------------

#### temperatur

Temperature measuring range, linear	-30...80 °C
-------------------------------------	-------------

#### Identification

Main design line	KNX
------------------	-----

## Instructions

---

Information text

Ensure correct orientation and free-standing installation.