



TG353

**IP44**



## Big support for KNX weather station

### Technical properties

#### Functions

Precipitation (Yes/No) 1 bit

#### Controls and indicators

Button / push-button with programming button

#### Voltage

Operating voltage over bus 21...32 V DC

#### Dimensions

Dimensions (LLxwwxhh) 40x16x6,5

Length, wall bracket 400 mm

#### Measurement

Measuring range, wind speed 0...35 m/s

#### Materials

Material aluminium

Material / surface powder-coated

#### LED control

LED with red programming LED

#### Installation, mounting

Installation mode for wall and mast assembly

#### Connection

Bus coupling unit with integral bus coupling unit

Type of connection with plug-in terminals for power supply

Bus connection bus connection via connecting terminal

#### Scope of delivery

Component with stainless steel screws for fastening

#### Equipment

Heating with heater element for winter operation

Slewing with an adjustable joint

#### Use

Differentiation characteristic 3 - Sales with integral bus coupling unit

#### Safety

Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-30...50 °C
<b>temperatur</b>	
Temperature measuring range, linear	-30...80 °C
<b>Identification</b>	
Main design line	KNX
<b>Instructions</b>	
Information text	Ensure correct orientation and free-standing installation.