



TH101

**Modular USB interface**

**Technical properties**

**Architecture**

Bus system EIB

**Configuration**

Number of modules 2

**Compatibility**

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

**Connectivity**

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

**Voltage**

Operating voltage over bus 21...32 V DC

**Dimensions**

Width of rail mounted device (RMD) 2 modules

**Power**

Total power loss under IN 0.15 W

Dissipated energy in cable 0.15 W

**Storage**

Data transmission rate 9.6 kBd

**Materials**

RAL colour RAL 7035 - Light grey

**Connection**

Connector type USB connector

**Cable**

USB cable length max. 5 m

**Settings**

Supported configuration modes system

Programming programmable from ETS3, V1.0

**Equipment**

Interface type USB

---

**Software**

---

|             |                                  |
|-------------|----------------------------------|
| Update      | with flash-controller technology |
| application | bus/PC connection                |

---

**Use conditions**

---

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

---

**Identification**

---

|                  |     |
|------------------|-----|
| Main design line | KNX |
|------------------|-----|

---