



SVN122

## Red LED Indicator light 230VAC

### Technical properties

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

#### Main electrical features

|                              |          |
|------------------------------|----------|
| Rated operational voltage Ue | 230 V    |
| Frequency                    | 50/60 Hz |

#### Voltage

|                                 |        |
|---------------------------------|--------|
| Rated insulation voltage        | 250 V  |
| Rated impulse withstand voltage | 4000 V |

#### Dimensions

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 62 mm   |
| Height of installed product | 83 mm   |
| Width of installed product  | 17.5 mm |

#### Frequency

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

#### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0.8 W |
|---------------------------|-------|

#### Materials

|        |     |
|--------|-----|
| Colour | red |
|--------|-----|

#### Lighting control

|              |     |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

#### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

#### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |

#### Use conditions

|  |             |
|--|-------------|
| Operating temperature                                    | -20...50 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3           |
| Altitude   | 2000 m      |
| Storage/transport temperature                            | -40...80 °C |