



TJA450

domovea Softwarelösung (Server + Client) mit USB/KNX Interface

Technical properties

Architecture

Fixing mode REG

Configuration

Number of modules 6

Controls and indicators

Indicator lamp yes

Manual selection switches / push-buttons Selection switch for online/offline mode

Connectivity

IP KNX server to supply up to 30 visualisation clients simultaneously with KNX data

Voltage

Auxiliary voltage 24 V DC

Operating voltage over bus 21...32 V DC

Electric current

Current consumption (operation) ≈ 150 mA

Dimensions

Width of rail mounted device (RMD) 6 modules

Power

Power consumption (operation) 1.5 W

Total power loss under IN 3.9 W

Storage

RAM 128 MB

Memory allocated to the icons/wallpapers 20 MB

Graphics memory ≈ 20 MB

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Material other

Material plastic

Type of surface treatment untreated

Connection

Number of IP cameras 10

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	Quickconnect
Settings	
Supported configuration modes	system
Scope of delivery	
Bus connection included	Yes
Accessories included	
Accessory for Android application	Yes
Accessory for IOS application	yes
Equipment	
Number of group	100
Number of controllable outputs	500
Number of clients	30
Number of energie measurement archives	100
Number of sequences	50
Number of USB interfaces	3
Processor	400 MHz
With configuration software	Yes
Software	
Client software	Yes
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Identification	
Main design line	KNX
Instructions	
Information text	Network technology skills are required for commissioning. System requirements: Windows XP, VISTA, Windows 7, Windows 8, Windows 10 (32 or 64-bit).