



TJA665

IP20

easy configuration tool

Technical properties

Architecture

Fixing mode	REG
-------------	-----

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Manual selection switches / push-buttons	Selection switch for online/offline mode
Button / push-button	with programming button and red programming LED

Voltage

Auxiliary voltage	24 V DC
Operating voltage	24 V DC
Operating voltage over bus	21...32 V DC

Electric current

Number of entry circuits	512
--------------------------	-----

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Connection

Conductor cross-section (flexible)	0.75...2.5 mm²
Conductor cross-section (rigid)	0.75...2.5 mm²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	easy
-------------------------------	------

Scope of delivery

Bus connection included	Yes
Contents of the kit	Configuration tool

Equipment

Number of outputs	512
Updateable	Yes
Visualization	No
Web-Server	Yes

Safety

Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX
Instructions	
Information text	Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.