



SVN331



Impulse 2NO Pushbutton

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Switching voltage	230 V

Electric current

Rated current	16 A
Momentary-contact current	16 A
Prospective short circuit withstand with MCB 16A B curve	1000A [Prot:16AcurveB]
Prospective short circuit withstand with fuse 16A gG	1000A [Prot:16AgG]
Thermal rated current outside of housings	16 A

Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C