



TJA665

IP20

easy configuration tool

Technical properties

Architecture

Fixing mode	REG
-------------	-----

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Manual selection switches / push-buttons	Selection switch for online/offline mode
--	--

Button / push-button	with programming button and red programming LED
----------------------	---

Voltage

Auxiliary voltage	24 V DC
-------------------	---------

Operating voltage	24 V DC
-------------------	---------

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Electric current

Number of entry circuits	512
--------------------------	-----

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm ²
---------------------------------	----------------------------

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Contents of the kit	Configuration tool
---------------------	--------------------

Equipment

Number of outputs	512
-------------------	-----

Updateable	Yes
------------	-----

Visualization	No
---------------	----

Web-Server	Yes
------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX
Instructions	
Information text	Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.