




TG308



LED kit for TXB344 (4 pcs)

Technical properties

Architecture

Bus system EIB

Functions

Bus module detachable No

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

Button / push-button with programming button and red programming LED

Main electrical features

Nominal voltage 1.8 V DC

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Maximum through current 300 mA

Dimensions

Depth of installed product 8 mm

Height of installed product 5 mm

Length 37 mm

Width of installed product 5 mm

Width of rail mounted device (RMD) 0 modules

Connection

Conductor cross-section (flexible) 0.75...2.5 mm²

Conductor cross-section (rigid) 0.75...2.5 mm²

Bus coupling unit with integral bus coupling unit

Type of connection with QuickConnect plug-in terminals

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Contents of the kit 4 red LEDs

Component

set consisting of 4 (low current) LEDs

Use

Differentiation characteristic 3 - Sales

with integral bus coupling unit

Safety

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Use conditions

Operating temperature

-5...45 °C

Identification

Main design line

KNX

Instructions

Special application information

for connection to universal interfaces with LED outputs