



TG500B

## Battery powered smoke detector - silver

### Technical properties

#### Functions

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m

#### Connectivity

Connection mode	hard-wired
-----------------	------------

#### Dimensions

Dimensions (LLxwxh)	125 mm x 48 mm
---------------------	----------------

#### Measurement

Detection Range	50 m <sup>2</sup>
-----------------	-------------------

#### Battery

life of battery	4 years
-----------------	---------

#### Power supply

Supply Voltage	1 battery 9V 6LR61
----------------	--------------------

#### Scope of delivery

Rechargeable battery backup included	No
--------------------------------------	----

#### Equipment

Sounder volume	85 dB
----------------	-------

#### Standards

Number of homologation to standard EC	0786-CPD-20390
Q-Label certification	No

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------