



TRC301B



## Radio Window contact battery-powered, KNX, Quicklink, White

### Technical properties

#### Functions

Bus module detachable	No
ETS additional functions	ETS additional functions: value, delay time, button function, battery condition
Function	easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)
Quicklink functions	quicklink functions: switching, blind, 2 scenes, time switching, NO contact push-button, forced control

#### Controls and indicators

Indicator lamp	lighting indicator
Button / push-button	with configuration button

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Voltage

Input voltage	3 V
Operating voltage	3 V DC

#### Electric current

Number of entry circuits	2
--------------------------	---

#### Dimensions

Depth of installed product	30 mm
Height of installed product	26 mm
Width of installed product	138 mm
Distance to magnet	max. 5 mm

#### Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

#### Battery

Battery service life [years]	≈ 4
------------------------------	-----

**Materials**

---

RAL colour	RAL 9010 - Pure white
------------	-----------------------

**LED control**

---

LED	with configuration LED ; with transmission status, battery status and control LEDs
-----	--

**Installation, mounting**

---

Mounting type	surface
---------------	---------

---

Installation mode	with adapters for magnet height compensation
-------------------	--

**Connection**

---

Type of connection	with additional screw terminals for wired reed contacts
--------------------	---

---

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

**Settings**

---

Programming	toolless quicklink configuration using buttons and LED display
-------------	--

**Scope of delivery**

---

Component	with adhesive pads for fastening
-----------	----------------------------------

**Equipment**

---

Number of outputs	0
-------------------	---

---

Number of radio channels	1
--------------------------	---

---

Number of quicklink links	max. 20 transmitter/receiver
---------------------------	------------------------------

**Use conditions**

---

Operating temperature	0...50 °C
-----------------------	-----------

---

Storage/transport temperature	-25...70 °C
-------------------------------	-------------