



TJA470

## IK04 IP20

### Domovea expert

#### Technical properties

##### Architecture

Fixing mode DIN rail type O (symmetrical)

##### Functions

Function converting

##### Configuration

Number of modules 6

##### Controls and indicators

With LED indication Yes

Manual selection switches / push-buttons Selection switch for online/offline mode

##### Connectivity

Protocol TCP/IP

Connectors / jacks with 2 USB sockets type A

IP Integration of IP cameras into the 2-wire system

##### Voltage

Operating voltage 24 V DC

Operating voltage 21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3

Operating voltage over bus 21...32 V DC

##### Electric current

Current consumption (operation) 0.5 A

Making current 650 mA

##### Dimensions

Width of rail mounted device (RMD) 6 modules

##### Power supply

Operating voltage via power supply 24 V DC

##### Equipment

Demounting protection No

Radio interface No

IR interface No

Updateable Yes

Visualization Yes

Web-Server Yes

**Use**

---

System technology	2-wire
-------------------	--------

**Safety**

---

Degree of contamination	2
-------------------------	---

---

Protection index IP	IP20
---------------------	------

---

Protection class	isol.class II
------------------	---------------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

---

Relative humidity (without condensation)	85 % at 25 °C
--	---------------