




TU418



**18-channel remote control**

**Technical properties**

**Functions**

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Dimensions**

Depth of installed product	16 mm
Height of installed product	133.6 mm
Dimensions (LLxwxh)	133,6 x 50,2 x 16 mm
Width of installed product	50.2 mm

**Frequency**

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

**Power**

Radio transmission power	< 10 mW
--------------------------	---------

**Equipment**

Number of radio channels	18
--------------------------	----

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Safety**

Protection index IP	IP30
---------------------	------

**Use conditions**

Operating temperature	0...45 °C
-----------------------	-----------