



TXA022

## Weekly time switch EASY, 2 modules

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

#### Electric current

Bus consumption	4 mA
-----------------	------

#### Dimensions

Depth of installed product	97 mm
Height of installed product	85 mm
Length	97 mm
Width of installed product	36 mm
Width of rail mounted device (RMD)	2 modules

#### Power

Total power loss under IN	0.3 W
Dissipated energy in cable	1 W

#### Battery

Lithium cell power reserve [years]	≈ 5
------------------------------------	-----

#### Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

#### Connection

Conductor cross-section (flexible)	1.5...10 mm <sup>2</sup>
Conductor cross-section (rigid)	1...6 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal

#### Settings

Number of program steps	56
Supported configuration modes	system
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Astro program	No

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Number of outputs	2
-------------------	---

---

Number of channels	2
--------------------	---

---

Supply failure reserve	lithium battery
------------------------	-----------------

---

With holidays program	Yes
-----------------------	-----

---

With random program	Yes
---------------------	-----

**Use**

---

Cycle	weekly
-------	--------

---

Differentiation characteristic 2 - Sales	with display
--	--------------

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	0...45 °C
-----------------------	-----------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Main design line	KNX
------------------	-----