



TRE302



**IP55**



**RF external double push button wall mounted**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, 1 up/down button control, push-button, 2 x alarm, status display

Quicklink functions quicklink functions: switching, dimming, blind, 2 scenes, switching time, push-button, NO contact

**Connectivity**

Radio protocol KNX Radio

Receiver category 2

**Electric current**

Number of entry circuits 2

**Dimensions**

Height of installed product 76 mm

Width of installed product 49 mm

**Frequency**

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

**Length**

Max distance to switches 3 mm

**Battery**

Battery service life [years] ≈ 5

**Materials**

Colour polarwhite

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Mounting type surface-mounted

Installation mode for vertical and horizontal mounting

**Cable**

Binary cable length max. 3 m

**Equipment**

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
<b>Safety</b>	
Protection index IP	IP55
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Storage/transport temperature	-20...70 °C