



TXA112

IP20

Power supply 30V DC 640 mA

Technical properties

Architecture

Bus system	EIB
------------	-----

Configuration

Number of modules	4
-------------------	---

Connectivity

Bus lines	1
-----------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	30 V
----------------	------

Output voltage	28...32 V
----------------	-----------

Filtered output voltage	30V +/- 2V
-------------------------	------------

Electric current

Output current	max. 640 mA
----------------	-------------

Output intensity	640 mA
------------------	--------

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Length	64 mm
--------	-------

Width of installed product	72 mm
----------------------------	-------

Power

Total power loss under IN	15 W
---------------------------	------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm ²
------------------------------------	---------------------------

Conductor cross-section (flexible)	0.75...2.5 mm ²
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm ²
---------------------------------	----------------------------

Type of connection	quick connect
--------------------	---------------

Equipment

Use

Differentiation characteristic 1 - Sales

with labelling field

Use conditions

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C