



TRM600



IP20

Control for latching relay, timer KNX radio

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Quicklink functions quicklink functions: time switching

Configuration

Number of modules 0

Controls and indicators

Indicator lamp yes

Connectivity

Radio protocol KNX Radio

Receiver category 2

Main electrical features

Frequency 50/60 Hz

Electric current

Number of entry circuits 0

Maximum through current 500 mA~

Momentary-contact current max. 0.5 A

Dimensions

Height of installed product 40 mm

Dimensions (LLxwwxhh) 40x40x18

Diameter 53 mm

Height 18 mm

Frequency

Transmission frequency 868 MHz

Radio reception frequency 868.3 MHz

Power

Total power loss under IN 150 mW

Power dissipation per coil 100 mW

Radio transmission power < 25 mW

Materials

Colour independent of design lines light grey

Surface appearance

mat

LED control

Max number of LED/CFL lamps 0

Connection

Conductor cross-section (flexible) 0.5...1.5 mm²

Conductor cross-section (rigid) 0.5...2.5 mm²

Type of connection with screw-in lift terminals

Settings

Supported configuration modes system, PB

Scope of delivery

Bus connection included No

Equipment

Number of outputs 1

Number of radio channels 1

Number of quicklink links max. 20 transmitter/receiver

Modular expandability No

Transmitter duty cycle 1 %

Use conditions

Operating temperature -15...45 °C

Storage/transport temperature -25...70 °C

Relative humidity (without condensation) 0...65 % (without condensation)