



TXA206A

Output 6 -fold 4A

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Multi-phase mode suitable to switch different external conductors

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Main electrical features

Rated operational voltage U_e 230 V

Rated current 4 A

Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

Electric current

Number of entry circuits 0

Maximum through current 4 A

Rated current 4 A

Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Output power 800 W

Max. switching power 4800 W

Materials

Colour stone grey

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 12 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 800 W

Connection

Bus coupling unit with integral bus coupling unit

Bus connection

bus connection via connecting terminal

Scope of delivery

Bus connection included Yes

Equipment

Number of outputs 6

Bidirectional radio frequency No

Modular expandability No

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX