



TXA206B

## Output 6 -fold 10A

### Technical properties

#### Architecture

Fixing mode Din-Rail

#### Functions

Multi-phase mode suitable to switch different external conductors

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Rated operational voltage  $U_e$  230 V

#### Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

#### Electric current

Number of entry circuits 0

Maximum through current 10 A

Rated current 10 A

#### Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 5 W

Output power 1200 W

Max. switching power 5400 W

#### Materials

Colour stone grey

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 1200 W

#### Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Number of outputs	6
-------------------	---

Bidirectional radio frequency	No
-------------------------------	----

Modular expandability	No
-----------------------	----

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Main design line	KNX
------------------	-----