



TXA114

**IP20**

**Power supply 1x 30V DC KNX + 1x 24V DC**

**Technical properties**

**Architecture**

Bus system	EIB
Fixing mode	Din-Rail

**Configuration**

Number of modules	4
-------------------	---

**Connectivity**

Bus lines	1
Outputs	one output 30 V DC, 320 mA incl. choke ; one output 24 V, 640 mA

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Voltage**

Output voltage	24V+30V
Output voltage	28...32 V

**Electric current**

Output current	max. 320 mA
Output intensity	320 mA

**Fuse**

Fuse	with electronic short-circuit and overload protection
------	---

**Dimensions**

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm
Width of rail mounted device (RMD)	4 modules

**Power**

Total power loss under IN	4.4 W
---------------------------	-------

**Materials**

RAL colour	RAL 7035 - Light grey
------------	-----------------------

**LED control**

LED	with green LED for display of power supply per output ; with red LED for display of short-circuit and overload protection per output
-----	--

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of connection	with QuickConnect plug-in terminals
Connection	protected earth conductor must be connected

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C