



TXA215

Dimmer 1 channel 1000W

Technical properties

Architecture

Bus system	KNX
Fixing mode	REG

Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors
Soft startup	bulb-preserving soft startup

Configuration

Number of modules	6
-------------------	---

Controls and indicators

With LED indication	Yes
Indicator lamp	yes
Operation	manual operation also possible without bus, e.g. on building site
Manual selection switches / push-buttons	selection switch for manual/bus operation as well as load setting

Main electrical features

Frequency	50/60 Hz
Rated current	4.3 A

Voltage

Auxiliary voltage	230 V AC
Input voltage	230 V AC
Operating voltage over bus	21...32 V DC

Electric current

Bus current consumption (data transfer)	2.3 mA
---	--------

Fuse

Fuse	overheating protection (display using LEDs)
------	---

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Power

Dimmable conventional transformers	20...1000 VA
Incandescent bulb power	20 / 1000 W
Total power loss under IN	10 W

Materials

Colour	stone grey
--------	------------

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	20...1000 W
--	-------------

Connection

Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Type of dimmer	universal
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise

Use

Local operation/hand operation	Yes
--------------------------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...60 °C

Identification

Main design line	KNX
------------------	-----