



TXA206A

## Output 6 -fold 4A

### Technical properties

#### Architecture

Bus system EIB

#### Functions

Multi-phase mode suitable to switch different external conductors

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Rated current 4 A

#### Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

#### Electric current

Number of entry circuits 0

Maximum through current 4 A

Rated current 4 A

#### Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Output power 800 W

Max. switching power 4800 W

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 12 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 800 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of contacts	6NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

---

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

---

**Equipment**

Number of outputs	6
Bidirectional radio frequency	No
Modular expandability	No

---

**Use conditions**

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

---

**Identification**

Main design line	KNX
------------------	-----