



TXA206B

Output 6 -fold 10A

Technical properties

Architecture

Bus system EIB

Functions

Multi-phase mode suitable to switch different external conductors

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Main electrical features

Rated operational voltage U_e 230 V

Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

Electric current

Number of entry circuits 0

Maximum through current 10 A

Rated current 10 A

Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 5 W

Output power 1200 W

Max. switching power 5400 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 1200 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of contacts 6NO

Bus coupling unit with integral bus coupling unit

Bus connection

bus connection via connecting terminal

Scope of delivery

Bus connection included Yes

Equipment

Number of outputs 6

Bidirectional radio frequency No

Modular expandability No

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX