



TXA207A

## Output 10 -fold 4A

### Technical properties

#### Architecture

Bus system	EIB
Fixing mode	Din-Rail

#### Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
Rated current	4 A

#### Voltage

Operating voltage over bus	21...32 V DC
Output voltage	230 V~
System supply voltage	30V DC via bus

#### Electric current

Number of entry circuits	0
Maximum through current	4 A
Rated current	4 A

#### Power

Max. power with electronic transfo.	800 W
Total power loss under IN	2.5 W
Output power	800 W
Max. switching power	8000 W

#### Materials

Colour	stone grey
--------	------------

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

#### Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of contacts	10NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Number of outputs	10
Bidirectional radio frequency	No
Modular expandability	No

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

**Identification**

Main design line	KNX
------------------	-----