



TXA207D

Output 10 -fold 16A

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Number of entry circuits	0
Maximum through current	16 A
Rated current	16 A

Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	10 W
Output power	2300 W
Max. switching power	14375 W

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	1500W - 200μF
--	---------------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Type of connection

quick connect

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	10
-------------------	----

Bidirectional radio frequency	No
-------------------------------	----

Modular expandability	No
-----------------------	----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Identification

Main design line	KNX
------------------	-----