



TXM632C



OUTPUT DEVICE FOR 12 SHUTTERS / BLINDS 230V~ 4A / NE

Technical properties

Architecture

Bus system	KNX
Number of blinds/shutters outputs	12

Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors
Function	with sun shade function ; with safety functions e.g. for wind, rain, alarm ; with positioning function for blind and lamella position
Operating mode	operating mode can be set for roller shutter/awning

Configuration

Number of modules	10
-------------------	----

Controls and indicators

Indicator lamp	yes
Operation	manual operation per channel using button (single-area operation) ; Manual operation can be activated via selection switch, thereby deactivation of the KNX function
Control	for activation of an AC drive per actuator channel
Indication / display	status LED integrated in the manual operation button
Manual selection switches / push-buttons	6 manual operation buttons for up/down per channel/device
Button / push-button	with illuminated programming button

Main electrical features

Type of supply voltage	AC
Frequency	50/60 Hz
Rated current	4 A

Voltage

Auxiliary voltage	230...240 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	7 mA
Bus current consumption (idle)	5 mA
Number of entry circuits	0
Maximum switching current	4 A

Dimensions

Width of rail mounted device (RMD)	10 modules
Height	90 mm

Power

Contact rating with 230 V in AC1	920 W
----------------------------------	-------

LED control

LED	Status LED integrated in manual operation button
-----	--

Connection

Connection cross-sect. flexible conductor	0,5 / 6mm ²
Connection cross-sect. rigid cable	0,5 / 6mm ²
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal
Type of connection	with screw

Settings

Supported configuration modes	system, easy
Setting	Switching time on change of direction is preset

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Modular expandability	No
-----------------------	----

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Device family	TXM
Main design line	KNX