


TXA304



## Binary input 4 fold, 230V~, modular, KNX

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Bus module detachable	No
-----------------------	----

Easy link functions	Switching functions, dimming functions, blind control functions, priority functions, scene functions, heating functions and timer functions
---------------------	---

ETS additional functions	ETS additional functions: value transmitter 1 and 2 bytes, 2-channel mode, level switch function
--------------------------	--

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Command by lighting push buttons	10 mA
----------------------------------	-------

#### Voltage

Input voltage	230 V
---------------	-------

Input voltage	230 V AC
---------------	----------

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Signal voltage	230 V AC
----------------	----------

#### Electric current

Number of entry circuits	4
--------------------------	---

#### Dimensions

Depth of installed product	69 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Length	35 mm
--------	-------

Width of installed product	71 mm
----------------------------	-------

Width of rail mounted device (RMD)	4 modules
------------------------------------	-----------

#### Length

Max distance to switches	100 mm
--------------------------	--------

#### Power

Total power loss under IN	0.1 W
---------------------------	-------

#### Materials

Colour	stone grey
--------	------------

Material	plastic
----------	---------

<b>Installation, mounting</b>	
Mounting type	din-Rail
<b>Connection</b>	
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Connection to	push-button / switch
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system
<b>Equipment</b>	
Number of outputs	0
<b>Safety</b>	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX