


TYA608C



## Output module 8x 16A /230V~, KNX

### Technical properties

#### Architecture

Bus system yes

#### Functions

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching for switching, e.g. of 8 independent loads or activation of 4 drives

Operating mode any combined operation from drive and switching functions possible

#### Configuration

Number of modules 6

#### Controls and indicators

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

#### Main electrical features

Rated current 16 A

#### Voltage

Auxiliary voltage 230 V AC

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

#### Electric current

Bus current consumption (data transfer) 15 mA

Bus current consumption (idle) 9 mA

Number of entry circuits 0

Maximum through current 16 A

Switching current at  $\cos \varphi = 0.8$  max. 16 A

**Dimensions**

Depth	65 mm
Width of rail mounted device (RMD)	6 modules
Height	90 mm

**Power**

Total power loss under IN	12 W
Output power	2300 W
Conventional transformers	1600 VA
Electronic transformers	1200 W

**Lighting control**

Fluorescent lamps with electronical ballast (EB)	20 x 36 W
- uncompensated	1200 VA

**Fluorescent bulbs control**

Energy-saving lamps	18 x 23 W
Power lighting fluo lamps	18x23W
Max. power fluo. duo lamp comp. series	20 x 36 W

**LED control**

Max number of LED/CFL lamps	18
230V LED lamps	18 x 23 W
Power LED	216 W
LED	Status LED integrated in manual operation button

**Incandescent bulbs control**

Max. power with incandescent lamps	2300 W
230 V incandescent lamps	2300 W
230 V halogen lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W

**Connection**

Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

**Settings**

Supported configuration modes	system
Setting	switching time on change of direction adjustable

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Modular expandability	No
-----------------------	----

Subject to technical modifications

Potential-free

with potential-free NO contacts as well as NC contact  
parameterisable

---

**Use**

Differentiation characteristic 3 - Sales

with plug-in terminals

---

**Safety**

Protection index IP

IP20

REACH conform

No

RoHS conform

Yes

Halogen free

No

---

**Use conditions**

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C