



TXA604D



Output module 4x 16A (C)/230V~, KNX

Technical properties

Architecture

Bus system yes

Functions

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching For switching, e.g. of 4 independent loads or activation of 2 drives

Operating mode any combined operation from drive and switching functions possible

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Rated current 16 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V AC

System supply voltage 30V DC via bus

Electric current

Bus current consumption (data transfer) 5 mA

Bus current consumption (idle) 3 mA

Number of entry circuits 0

Maximum through current 16 A

Rated current 16 A

Dimensions

Width of rail mounted device (RMD)	4 modules
Height	90 mm

Power

Max. power with electronic transfo.	1200 W
Output power	2300 W
Max. switching power	5750 W
Conventional transformers	1600 VA
Electronic transformers	1200 W

Lighting control

Fluorescent lamps with electronical ballast (EB)	20 x 36 W
- uncompensated	1200 W

Fluorescent bulbs control

Energy-saving lamps	23 W
Power lighting fluo lamps	18x23W
Fluorescent lamps parallel compensated	1500 W /200 µF

LED control

Max number of LED/CFL lamps	18
230V LED lamps	18 x 23 W
Power LED	216 W
LED	Status LED integrated in manual operation button

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of load	C-Load
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Type of contacts	4NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

Settings

Supported configuration modes	easy, system
Setting	Switching time on change of direction is preset

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	4
Modular expandability	No

Use

Differentiation characteristic 3 - Sales	with plug-in terminals
--	------------------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Device family	TXA
Main design line	KNX