




TYA661B



**Dimmer 1 channel 600W**

**Technical properties**

**Architecture**

Fixing mode REG

**Functions**

Bus module detachable No

Multi-phase mode suitable to switch different external conductors

Soft startup bulb-preserving soft startup

**Configuration**

Number of modules 4

**Controls and indicators**

With LED indication Yes

Indicator lamp yes

Operation manual operation also possible without bus, e.g. on building site

Manual selection switches / push-buttons selection switch for manual/bus operation as well as load setting

**Main electrical features**

Frequency 50/60 Hz

Rated current 4 mA

**Voltage**

Auxiliary voltage 230 V AC

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

**Electric current**

Bus current consumption (data transfer) < 2.3 mA

**Fuse**

Fuse overheating protection (display using LEDs)

**Dimensions**

Width of rail mounted device (RMD) 4 modules

**Power**

Dimmable conventional transformers 600 VA

Incandescent bulb power 600 W

Total power loss under IN 320 mW

Power dissipation per coil 180 mW

**Fluorescent bulbs control**

Dimmable energy-saving lamps	120 W
Power lighting fluo lamps	120W

**LED control**

Quantity of dimmable, 230 V retrofit LED lamps	max. 10
Max number of LED/CFL lamps	10
Dimmable LED lamps	60 W
Dimmable 230 V retrofit LED lamps	per channel 60 W
Power LED	120 W

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps	600 W
--	-------

**Connection**

Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

**Settings**

Supported configuration modes	system
-------------------------------	--------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Type of dimmer	dimming actuator
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise

**Use**

Local operation/hand operation	Yes
--------------------------------	-----

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

**Identification**

Main design line	KNX
------------------	-----