



TYB602A



**IP20**

## 2 flush mounted output 4A twisted pair

### Technical properties

#### Architecture

Bus system	KNX
Fixing mode	flush-mounting

#### Configuration

Number of modules	0
-------------------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	4 A

#### Voltage

Max. switching capacity at	230 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

#### Electric current

Bus current consumption (data transfer)	≈ 7 mA
Bus current consumption (idle)	5 mA
Number of entry circuits	0
Maximum through current	4 A
Rated current	4 A
Switching current at $\cos \varphi = 0.8$	max. 4 A

#### Dimensions

Height of installed product	29 mm
Dimensions (Ø x H)	53 x 29 mm
Width of rail mounted device (RMD)	0 modules
Height	29 mm

#### Power

Max. power with electronic transfo.	600 W
Output power	500 W
Max. switching power	1000 W
Conventional transformers	600 VA
Electronic transformers	per channel 600 W

<b>Materials</b>	
Colour	light grey
<b>Lighting control</b>	
Fluorescent lamps with electronical ballast (EB)	6 x 58 W
<b>Fluorescent bulbs control</b>	
Energy-saving lamps	6 x 18 W
Power lighting fluo lamps	6 x 18W
Max. power fluo. duo lamp comp. series	12 x 36 W
<b>LED control</b>	
Power LED	108 W
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	600 W
230 V incandescent lamps	600 W
230 V halogen lamps	600 W
230 V incandescent lamps and halogen lamps	600 W
<b>Connection</b>	
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system
<b>Scope of delivery</b>	
Bus connection included	Yes
<b>Accessories included</b>	
Box	installation in flush-mounted or splash-protected junction box
<b>Equipment</b>	
Modular expandability	No
<b>Use</b>	
Differentiation characteristic 3 - Sales	with screw-in lift terminals
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	

Subject to technical modifications

