



TXA610D



**Output module 10x 16A (C)/230V~, KNX**

**Technical properties**

**Architecture**

Bus system yes

**Functions**

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching For switching, e.g. of 10 independent loads or activation of 5 drives

Operating mode any combined operation from drive and switching functions possible

**Configuration**

Number of modules 6

**Controls and indicators**

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

**Main electrical features**

Rated operational voltage  $U_e$  230 V

Rated current 16 A

**Voltage**

Operating voltage over bus 21...32 V DC

Output voltage 230 V AC

System supply voltage 30V DC via bus

**Electric current**

Bus current consumption (data transfer) 6 mA

Bus current consumption (idle) 4 mA

Number of entry circuits 0

Maximum through current 16 A

Rated current 16 A

**Dimensions**

Width of rail mounted device (RMD)	6 modules
Height	90 mm
<b>Power</b>	
Max. power with electronic transfo.	1200 W
Total power loss under IN	1.5 W
Power dissipation per coil	0.15 W
Output power	2300 W
Max. switching power	14375 W
Conventional transformers	1600 VA
Electronic transformers	1200 W
<b>Lighting control</b>	
Fluorescent lamps with electronical ballast (EB)	20 x 36 W
- uncompensated	1200 W
<b>Fluorescent bulbs control</b>	
Energy-saving lamps	23 W
Power lighting fluo lamps	18x23W
Fluorescent lamps parallel compensated	1500 W /200 µF
<b>LED control</b>	
Max number of LED/CFL lamps	18
230V LED lamps	18 x 23 W
Power LED	216 W
LED	Status LED integrated in manual operation button
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W
<b>Connection</b>	
Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	C-Load
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of contacts	10NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	easy, system
Setting	Switching time on change of direction is preset
<b>Scope of delivery</b>	
Bus connection included	Yes

Subject to technical modifications

**Equipment**

Number of outputs	10
Modular expandability	No

**Use**

Differentiation characteristic 3 - Sales	with plug-in terminals
--	------------------------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

**Identification**

Device family	TXA
Main design line	KNX