




TXA624C



## OUTPUT DEVICE FOR 4 SHUTTERS / BLINDS 230V~ 6A / NE

### Technical properties

#### Architecture

Bus system	KNX
Number of blinds/shutters outputs	4
Fixing mode	REG

#### Functions

Bus module detachable	No
Multi-phase mode	suitable to switch different external conductors

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	4 manual operation buttons for up/down per channel/device

#### Main electrical features

Type of supply voltage	AC
Frequency	50/60 Hz
Rated current	6 A

#### Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

#### Electric current

Bus current consumption (data transfer)	5 mA
Bus current consumption (idle)	3 mA
Number of entry circuits	0
Maximum switching current	6 A
Switching current at $\cos \varphi = 0.6$	max. 6 A

#### Dimensions

Width of rail mounted device (RMD)	4 modules
Height	90 mm

#### Power

Contact rating with 230 V in AC1	1200 W
----------------------------------	--------

#### Materials

Colour light grey

---

**Connection**

Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Number of contacts	4
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

---

**Settings**

Supported configuration modes system

---

**Scope of delivery**

Bus connection included Yes

---

**Equipment**

Modular expandability No

---

**Safety**

Protection index IP IP20

---

**Use conditions**

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

---

**Identification**

Main design line KNX