



VE106F

**Enclosure,vector, IP5x, 6M**

**Technical properties**

**Functions**

|                     |     |
|---------------------|-----|
| With a pipe-in lead | Yes |
|---------------------|-----|

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

**Compatibility**

|                         |    |
|-------------------------|----|
| Suitable for Multimedia | No |
|-------------------------|----|

**Main electrical features**

|                 |       |
|-----------------|-------|
| Nominal voltage | 400 V |
|-----------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Dimensions**

|                                |        |
|--------------------------------|--------|
| Depth of installed product     | 113 mm |
| Internal depth                 | 113 mm |
| Height of installed product    | 190 mm |
| Width of installed product     | 165 mm |
| Width in division units        | 6      |
| Thickness of sidewall material | 2.5 mm |

**Cover, door**

|                                    |                |
|------------------------------------|----------------|
| Identification of protection index | 65             |
| Interlockable                      | No             |
| Number of keylock of the door      | 0              |
| Cover type                         | Closed (plain) |
| Door locking                       | without        |
| Door leave                         | single         |
| Cover type                         | Door           |
| Transparent cover or door          | No             |

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | light grey            |
| RAL colour                | RAL 7035 - Light grey |
| Type of surface treatment | untreated             |

**Installation, mounting**

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Connection**

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 3 |
|--------------------------|---|

**Settings**

|                |                           |
|----------------|---------------------------|
| Enclosure type | Distributor empty cabinet |
|----------------|---------------------------|

**Equipment**

|                                      |     |
|--------------------------------------|-----|
| Number of rows                       | 1   |
| Quantity of section in width         | 1   |
| Number of keys                       | 1   |
| Quantity of rails                    | 1   |
| Can be accessorized                  | Yes |
| Number of openings for flange plates | 16  |
| Extension possible                   | No  |
| Earthing terminal block              | Yes |
| Neutral terminal block               | No  |
| Signal passing door                  | Yes |

**Standards**

|                    |        |
|--------------------|--------|
| GWT Glow wire test | 750 °C |
|--------------------|--------|

**Safety**

|   |               |
|---|---------------|
| IK protection code against mechanical impacts | IK07          |
| Protection class                              | isol.class II |
| REACH conform                                 | No            |
| RoHS conform                                  | Yes           |
| Halogen free                                  | No            |
| Impact strength                               | IK07          |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|