



VE106F

**Enclosure,vector, IP5x, 6M**

**Technical properties**

**Functions**

With a pipe-in lead	Yes
---------------------	-----

**Configuration**

Number of modules	6
-------------------	---

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Main electrical features**

Nominal voltage	400 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	113 mm
Internal depth	113 mm
Height of installed product	190 mm
Width of installed product	165 mm
Width in division units	6
Thickness of sidewall material	2.5 mm

**Cover, door**

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polystyrol (PS)
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

Subject to technical modifications

---

**Connection**

Number of conduit inlets	3
--------------------------	---

---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

---

**Equipment**

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Number of keys	1
----------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	16
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	No
------------------------	----

Signal passing door	Yes
---------------------	-----

---

**Standards**

GWT Glow wire test	750 °C
--------------------	--------

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

IK protection code against mechanical impacts	IK07
---	------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

---

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------